

## FAQs

- How do you fit a ClearCap™ ?

Use our Models Available page to find the most common listings. If you don't see your model, measure the overhead guards outside edges, width by length. Using the Listings by Dimensions page, find the closest ClearCap™ that will fit over your dimensions or call us at 614-583-5749 with your make, model and dimensions and we will help you select the proper ClearCap.™

- How do I order ClearCaps™ ?

You can order through our website. We gladly accept all major credit cards. If you prefer, we have friendly and knowledgeable customer service reps that can assist you with all your questions, call us at 614-583-5749. Our office hours are 8AM-5PM EST.

- What are ClearCaps™ made of and how do they hold up?

ClearCaps™ are made from Ultra Tuff SG weatherable polycarbonate. This heavy-duty plastic material is rigid, sturdy and UV resistant, it does not yellow over time. It is the same impact resistant material used in riot gear, safety glasses and protective shields. Both clear and tinted ClearCaps™ block 100% of UV light, protecting operators from skin-damaging sunlight.

- How do ClearCaps™ ship?

ClearCaps™ ship from our manufacturing facility F.O.B Salt Lake City, UT via ground delivery or common carrier depending on volume. We always utilize the most cost-effective shipping available. We ship prepaid and added to your invoice.

- How long does it take to receive my ClearCaps™ ?

Most ClearCaps™ arrive within seven business days after order placement.

- How long do ClearCaps™ last and do they come with a warranty?

All units are warranted to be free from defects in materials or workmanship of one year from delivery to the buyer when properly installed, used, maintained and serviced in accordance with directions and instructions provided upon receipt. We do not warranty against misuse or abuse. We have had units in the field now for many years without any problems. Be sure to check your fit BEFORE removing the protective film, no returns are possible once the film is removed.

- How do ClearCaps™ attach?

Each unit is slotted at four points. Four high tension nylon web straps with cam lock buckles are provided. No drilling or tapping of the cage is required, simply loop the webbing through the slots and around the cage and lock them tight. This tool free installation takes only a few seconds.